

Zoo Portable Candler

NEW! Used By Professionals
in the Field!



Now Candle Your Eggs at the Nest or in the Field!

Don't risk valuable eggs with unnecessary movement, handling, and temperature variations. Shorten the time away from the nest! If this unit saves just one valuable egg *it is worth the price!*

Zoos, animal parks, breeders, and conservationists should have one of these units.

*Includes Complete Set of
Four Light Apertures for Different Size Eggs!*



- ♥ Totally Portable/Battery Operated
- ♥ Rechargeable
- ♥ Hi Intensity Halogen Bulb
- ♥ Exhaust Cooling Fan
- ♥ Variable Light Intensity
- ♥ Many Other Professional Features
- ♥ One Hour Candling Time
- ♥ Four Hour Full Charge Time

CATALOG NUMBER	DESCRIPTION	VOLTAGE
910-117	Zoo Portable Candler	120 VAC
910-118	Zoo Portable Candler	230 VAC


Hi-Intensity Egg Candler

The Hi-Intensity Candler is the most powerful and effective egg candler we have ever produced. It has an intense narrow beam light source with a prescribed focal length. This light source gives maximum light penetration into the egg, making it highly effective on dark and mottled eggs. The light is so bright that it should not be viewed with the naked eye. The long life lamp is supplied by a heavy duty transformer and the unit is air cooled to minimize heat. A control is provided to vary the light intensity over its upper range, only the amount of light required should be used. Operating the halogen lamp at less than full intensity can extend lamp life significantly. The light tube and the supplied aperture adapters make the unit compatible for small, medium and large eggs.

Ostrich eggs have been successfully candled with this unit. Chicken and Turkey eggs can be candled without the need of a darkened room. This unit is also an excellent unit for candling game and exotic bird eggs. The Hi-Intensity Candler is ideal for laboratories and zoos. **Note: Will not candle Emu eggs.**

CATALOG NUMBER	VOLTAGE	HERTZ
950-076	120 VAC	50/60
950-077	230 VAC	50/60
SPECIAL ZOO MODEL (Ultra Hi-Intensity)		
950-104	120 VAC	50/60
950-105	230 VAC	50/60

Add Suffix "A" for Australian Power Cord
Add Suffix "F" for West European Style Power Cord




Adapters Included

**One Of The
Best Candles Available!**



Egg Candles

Econo Egg Candler



Candles incubating eggs to determine whether embryos are developing. Also used to check for blood spots in food eggs. The light of a 100 Watt bulb is concentrated into the egg through an orifice over which the egg is set. To prevent overheating, a push button switch turns the light off when released. A simple cost effective unit used by hobbyist.

Catalog No. 950-107 (120 VAC)
950-108 (230 VAC)

Hi-Power Egg Candler



The Hi-Power Egg Candler is an economical unit that is widely used by hatcheries to check egg fertility. Egg producers use it to check egg quality, laboratories use the candler to check embryos and pharmaceutical manufacturers use it to check vaccines in production. This unit has a variable intensity control enabling the operator to select the amount of light desired, thus reducing eye strain and producing adequate candling power. The Hi-Power Egg Candler is supplied with one candler and an extra bulb. The unit has sufficient reserve power to operate two candlers at the same time, increasing productivity.

Catalog No. 950-070 (120 VAC)
950-071 (230 VAC)
Extra Candling Wand - 900-110

Standard Egg Tester



The best in low cost candlers. Compact hand unit with 8 foot cord is similar to the Cool-Lite Tester, but without the automatic on/off feature. Recommended for general use, the Standard Egg Tester gives good efficiency yet uses a 6 watt bulb for low operating temperatures. 230 Volt unit shipped without plug on the power cord. 50/60 Hertz

Catalog No. 950-015 (120 VAC)
950-079 (230 VAC)

Cool-Lite Tester




A compact, efficient egg tester. Has an effective beam using only 6 Watts of power. This tester has an internal Mercury switch which automatically activates the light when picked up, competitor's units do not have this important feature. Cool-Lite can be easily moved over eggs for testing without handling the eggs. Comes with an 8' power cord. 230 Volt unit shipped without plug on power cord. 50/60 Hertz.

Catalog No. 950-014 (120 VAC)
950-078 (230 VAC)

Probe Lite

The Probe-Lite is ideal for candling eggs right in the nest or in an incubator. Infertile eggs can be removed so fertile eggs do not become contaminated or spoiled should the infertile egg break or spoil. A great tool to monitor and check embryo development and detect slightly damaged eggs (hairline cracks) which can possibly be repaired. Battery operated.

Catalog No. 920-046 
Replacement Bulb - 240-080



NEW!
Replacement Bulb
Catalog No. 240-001

